



Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Ring Tongue**

Wire Size: **509 – 3260 CMA**

Stud Size: **#4, M2.5**

Features

Product Type Features

Shape Description	RING-048
Stud Size	#4, M2.5
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	180 °

Body Features

Inspection Slot	No
Weight per Piece	.689 g

Contact Features

Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Closed
Terminal Orientation	Offset
Terminal Plating Material	Tin



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	3.02 mm[.119 in]
Tongue Thickness	.79 mm[.031 in]
Overall Product Length	16.59 mm[.653 in]
Barrel Inside Diameter	1.55 mm[.061 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin
Heavy Duty	No

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free






Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58545-1 SOLISTRAND 10-22 DIE ASSY	 TE Part # 49935 DAHT SOLIS 22-10 ASSY	 TE Part # 58546-1 PC 22-10 SOLISSPICE SPL I SHT	 TE Part # 217200-1 626 STRGHT ACT HD,NORM CLOSED
 TE Part # 525693 DAHT SOLIS 22-10 ASSY	 TE Part # 58545-3 SDE DIE ASSY. 22-10 SOLISTRAND	 TE Part # 189989-1 22-10 SOLISTRAND PNEU HD	 TE Part # 47812 DIES SOLIS 22-16 DIE SET
 TE Part # 539662-2 MATR SOLISTR 0,3-6,	 TE Part # 169400 CERTI-LOK FRAME W/O DIES		

Customers Also Bought





TE Part #53123-2
TERMINAL,SOLIS SPR SPD 16-14 6



TE Part #485043-2
SPLICE 4000-9000 .020 TPBR



TE Part #53126-2
TERMINAL,SOLIS SPR SPD 12-10 6



TE Part #3-1617033-1
HFW1230K06P = M39016/6-105P



TE Part #2267088-7
RAS1R102VS2RES



TE Part #326875
PIDG RING TONGUE TERMINALS



TE Part #2-35476-1
TERMINAL,SOLIS R 12-10 6

Documents

Product Drawings

SOLIS R 22-16 COMM 22-18 MIL 4

English

CAD Files

Customer View Model

ENG_CVM_CVM_323096_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_323096_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_323096_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English

UL Report

English

323096

Ring Terminals & Spade Terminals, Ring Tongue, 22 – 16 AWG Wire Size, .26 – 1.65 mm² Wire Size, 509 – 3260 CMA Wire Size, Stud Size #4 / M2.5

