

KERN EFS 5000-0S05

KERN

Perfect school balances for experimental teaching - easy to use, space-saving, stackable



Category	
Brand	KERN
Product category	Laboratory balances
Product group	School balances

Measuring System	
Readability [d]	1 g
Weighing capacity [Max]	5200 g
Number of weighing ranges	1
Eccentric loading at 1/3 [Max]	3 g
Reproducibility	1 g
Linearity	± 3 g
Linearisation in dots	2
Weighing system	Strain gauge
Resolution	5.200
Units	g gn dwt oz t lb oz
Default unit	g
Stabilization time	2,5 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	5 kg (M2)
Possible calibration points	5 kg

Approval	
CE mark	✓

Display	
Display type	LCD
Display digit height	15 mm
Display backlight	no
Display screen size	55×23 mm

Languages of the user interface	Symbol language
---------------------------------	-----------------

Construction	
Dimension housing (W×D×H)	145×205×46,5 mm
Dimensions weighing platform (W×D×H)	130×125×10 mm
Dimensions weighing surface (Ø)	120 mm
Dimensions weighing surface (W×D)	134×127 mm
Material housing	plastic
Material display housing	Plastics
Material weighing plate	plastic
Material platform	Plastics

Functions	
Number of keys for operation	2
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 1 min 30 sec
Capacity display	✓
Tare function	manual (multi)
IP protection - complete device	-

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	6 V, 1 A
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Battery
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight off	50 h
Battery	4×1.5 V AA
Battery operating time	200 h

Environmental conditions	
Humidity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	255×200×70 mm
Net weight approx.	0,55 kg
Gross weight approx.	3,0 kg

KERN EFS 5000-0S05



Perfect school balances for experimental teaching - easy to use, space-saving, stackable

Services (optional)

Article number for adjustment at the location of installation 961-248

Piktogramme

STANDARD



OPTION

