

40763 ✓ ACTIVE

TE Internal #: 40763


Ring Terminals & Spade Terminals, Spade Tongue, 20 – 16 AWG

Wire Size, .5 – 1.4 mm² Wire Size, 1021 – 2582 CMA Wire Size, Stud Size M3.5 / #6

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Spade Tongue**

Wire Size: **1021 – 2582 CMA**

Stud Size: **#6, M3.5**

Features

Product Type Features

Shape Description	Square Spade
Stud Size	#6, M3.5
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Terminal Angle	180 °
----------------	-------

Body Features

Inspection Slot	No
Weight per Piece	.426 g

Contact Features

Contact Base Material	Brass
Ring & Spade Terminal Type	Spade Tongue
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin



Contact Underplating Material	Nickel
-------------------------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.09 in
Wire Size	1021 – 2582 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.51 mm[.02 in]
Overall Product Length	19.05 mm[.75 in]
Barrel Inside Diameter	1.52 mm, 3.17 mm[.06 in][.125 in]
Accepts Wire Insulation Diameter (Max)	3.3 mm[.13 in]
Accepts Wire Insulation Diameter Range	2.29 – 3.3 mm[.09 – .13 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Heavy Duty	No

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	15000
Packaging Method	Strip/Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 42318-2
SPADE TERMINAL TERMINAL 20-16 AWG TPBR



TE Part # 2-2150693-1
OCEAN_2.0_Applicator-E-110F155F



TE Part # 2-2150693-2
OCEAN_2.0_Applicator-E-110F155F



TE Part # 2150693-1
OCEAN_2.0_Applicator-E-110F155F




TE Part # 2150693-2
OCEAN_2.0_Applicator-E-110F155F



TE Part # 7-2150693-1
OCEAN_2.0_Applicator-E-110F155F



TE Part # 7-2150693-2
OCEAN_2.0_Applicator-E-110F155F



KIT
REPRESENTATION ONLY
TE Part # 7-2150693-7
OCEAN_2.0_SPARE_PART_KIT-110F155F

Customers Also Bought



TE Part #6609021-7
5VB1=F7126 S0



TE Part #1-480278-0
12P CMNL CAP HSG P/M NATL



TE Part #2-520263-4
ULTRA-FAST 250 ASY REC 22-18 TPBR



TE Part #3-520140-4
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR



TE Part #62650-1
250 FASTON TAB TPBR



TE Part #2-520334-2
ULTRAFast 187 ASSY FLAG REC 22-18 TPBR




TE Part #T4110002081-000
M12,FEMALE,STRAIGHT,A CODE,8P,PG9,GOLD



TE Part #7-1393117-8
KUP-14A15-120=KU



TE Part #2-172076-7
POSITIVE LOCK 250 HOUSING RECEPTACLE



TE Part #GAG10K3D116
PRO2-PROBE

Documents

Product Drawings

[SPADE 138\(3.50MM\)TERMINAL 20-16 AWG TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_40763_AG_c-40763-ag.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_40763_AG_c-40763-ag.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_40763_AG_c-40763-ag.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Engineering Report

English