

## Features

- Compliance to Lighting and LED Equipment Regulations
- IP20 for Indoor Installation
- MM Marking for Furniture Installation
- Suitable for LED Lighting Applications
- 1 Year Warranty



## Marks / Approvals



Image similar, variations possible

## Specifications

MODEL No.	Voltage	Min. Load	Max. Load	Max. Power	Ripple & Noise
SSL60-12VF	12 V	0.00 A	5.00 A	60 W	< 380mV p-p
SSL60-24VF	24 V	0.00 A	2.50 A	60 W	< 380 mV p-p
INPUT	<b>Voltage</b>	AC 198 V – 264 V			
	<b>Frequency</b>	50 Hz - 60 Hz			
	<b>Current (rms max)</b>	< 0.5 A			
	<b>Power Factor</b>	≥ 0.97			
PROTECTION	<b>Overload</b>	Yes, Auto Recovery			
	<b>Overvoltage</b>	Yes,			
	<b>Short Circuit</b>	Yes, Auto Recovery			
	<b>Over Temperature</b>	Yes, temperature exceeding max. value at detection point			
	<b>Input Surge Current</b>	< 70 A			
OTHERS	<b>Cooling</b>	Convection Cooling			
	<b>Efficiency</b>	≥ 89 % typical			
	<b>Startup Time</b>	< 0.5 s			
	<b>Protection Marking</b>	IP20 (IEC 60529)			
	<b>Working Noise</b>	< 35 dB, pickup at 10 cm			
	<b>Protection Class</b>	Class II			
	<b>Case Material</b>	Plastic cover with terminal block Input: H03VVH2-F 2x0.75mm <sup>2</sup> ; Output: H03VVH2-F 2x1.00mm <sup>2</sup>			
Environment	<b>Temperature</b>	Operating: -20 °C to 45 °C / Max. Case Temperature: 90 °C			
	<b>Humidity</b>	Operating: 45 % RH to 85 % RH			
Lifetime	30 000 hrs at max. Ta, rated input voltage, output max. rated power				
SAFETY	IEC / EN 61347-1, IEC / EN 61347-2-13, IEC 60598				
EMI	EN 55015				
EMS	EN 61547				
Harmonic	EN 61000-3-2 Class C				
Case Dimensions	304.6 mm x 30 mm x 16.7 mm				

