

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0872640652

Status:


Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch Milli-Grid Receptacle, Side Entry, Through Hole, 0.38µm Gold (Au)
Selective Plating, 6 Circuits, Lead-Free



Documents:

3D Model

Drawing (PDF)

Product Specification PS-87264-001 (PDF)

Application Specification 503940001-AS-000 (PDF)

Packaging Specification PK-87264-0001-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Receptacles
Series		87264
Application		Board-to-Board, Signal
Component Type		PCB Receptacle
Overview		Milli-Grid Connector System
Product Name		Milli-Grid
Taxonomy		PCB Headers and Receptacles
UPC		822348473786

Physical	
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.205/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.55mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

87264 Series

Mates With

87758 , 87759 , 87760

Solder Process Data

Duration at Max. Process Temperature (seconds)	014
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265

Material Info

Reference - Drawing Numbers

Application Specification	503940001-AS-000
Packaging Specification	PK-87264-0001-001
Product Specification	PS-87264-001
Sales Drawing	SD-87264-XX50-001

This document was generated on 01/20/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION