

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2005290220

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, 1.90mm Height, Single Bottom Contact (FS19), Right-Angle, Surface Mount, ZIF, 22 Circuits



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification 2005290000-000 (PDF)

Packaging Specification 2005299200-200 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Overview

Product Name

Taxonomy

UPC

FFC/FPC Connectors

200529

Black Actuator

Easy-On FFC FPC Connectors

Easy-On

FFC / FPC Connectors

889056681926

Physical

Actuator Type

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Contact Position

Durability (mating cycles max)

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Temperature Range - Operating

Wire/Cable Type

Front Flip

22

22

Beige

Bottom

25

1.90mm

Phosphor Bronze

Tin-Silver-Bismuth

Tin-Silver-Bismuth

Liquid Crystal Polymer

259.573/mg

1

Right Angle

No

Surface Mount

Yes

Embossed Tape on Reel

1.00mm

1.00mm

1.016µm

1.016µm

Yes

No

-40° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.0A

125V

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

2005299200-200

2005290000-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series
200529 Series

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION