

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5023820570

Status:


Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, Tin Plating, 5 Circuits



Documents:	
Drawing (PDF)	Application Specification AS-502380-002-001 (PDF)
3D Model	Packaging Specification SPK-502382-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-502382-001-001 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Receptacles
Series	502382
Application	Signal, Wire-to-Board
Component Type	PCB Receptacle
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
Taxonomy	PCB Headers and Receptacles
UPC	822350895224
Physical	
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	7.80mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	271.601/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

502382 Series

Mates With

502380 CLIK-Mate Housing

Voltage - Maximum	50V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-502380-002-001
Packaging Specification	SPK-502382-001-001
Product Specification	PS-502382-001-001
Sales Drawing	SD-502382-001-001, SD-502382-001-002, SD-502382-001-003, SD-502382-003-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION