



Softtherm 6000

high thermal conductivity

Applications

- ◆ DC-DC converter, power tools
- ◆ electric vehicles
- ◆ high energy rechargeable batteries

Benefits

- ◆ low hardness
- ◆ elastic
- ◆ good aging behavior
- ◆ good handling

Properties	Unit	Softtherm 6000
Colour		pink
Basic material		silicone
Thermal Properties		
Thermal resistance R_{th}	K/W	0.41
Thermal conductivity λ	W/mK	6.0
Electrical Properties		
Breakdown voltage $U_{d; ac}$	kV	8
Dielectric breakdown $E_{d; ac}$	kV/mm	8
Mechanical Properties		
Measured thickness (+/-10%)	mm	1.000
Hardness	Shore 00	55-75
Physical Properties		
Application temperature	°C	-40 to +200
Density	g/cm ³	3.18
Flame rating	UL-94	V-0
Possible thickness	mm	TBD

Measured @ thickness 1mm

The Keratherm®-Softtherm® 6000 is characterized by very good thermal and dielectric properties. Due to its very good elastic and adaptable behaviour, the 6000 is also very suitable for pressure sensitive applications.

Data for engineer guidance only.
Observed performance varies in application.
Engineers are reminded to test the material in application.

*Kerafol test according to UL

NOTE:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. KERAFOL® is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. All specifications are subject to change without notice. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded. In case KERAFOL® would be nevertheless held liable, on whatever legal ground, KERAFOL®'s liability will in no event exceed the amount of the concerned delivery. All KERAFOL® products are sold pursuant to the KERAFOL®'s Terms and Conditions of sale and delivery in effect from time to time, a copy of which will be furnished upon request.

08-2022