

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757575121

Status:

Active

Overview:

Description:

MX150 Dual Row Header, Vertical, 4 Circuits, 2.50µm Tin (Sn) Plating, 16.09mm Mating Pin Length, 3.05mm PC Tail Length

General	
Product Family	PCB Headers
Series	75757
Application	Power, Wire-to-Board
Component Type	PCB Header
Overview	mx150_sealed_connector_system
Product Name	MX150
Taxonomy	PCB Headers and Receptacles
UPC	800756794761

Physical	
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.107/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

75757 Series

Mates With

33472 Dual Row MX150 Receptacles

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-340-001
Product Specification	PS-75757-000-001
Sales Drawing	SD-75757-002-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION