## KERN ABP 200-5AM



Premium analytical balance with the latest Single-Cell Generation for extremely rapid, stable weighing results - now also as a version with automatic sliding doors



С	at	е	g	0	ry
			$\circ$		• •

CE mark

Outegory	
Brand	KERN
Product category	Laboratory balances
Product group	Analytical balances
Measuring System	
Readability [d]	0,00001 g
Readability carat [d] (ct)	0,0001 ct
Weighing capacity [Max]	220 g
Minimum weight [Min] (ct)	0,1 ct
Weighing capacity [Max] (ct)	1100 ct
Eccentric loading at 1/3 [Max]	0,0003 g
Minimum weight [Min]	0,001 g
Reproducibility	0,000015 g; 0,00003 g; 0,00005 g
Linearity	± 0,0002 g
Weighing system	Single-Cell
Resolution	22.000.000
Tare range	220 g
Units	g mg ct
Units (if device is conformity assessed)	g mg ct
Default unit	g
Stabilization time	8 s
Warm-up time	8 h
Adjustment options	Internal calibration (automatic) Adjusting with internal weight (manual)
Approval	
	,

Conformity assessment possible 1 ex works Pattern approval for conformity ./ assessment Accuracy classe I 0,001 g Verification scale interval [e] Verification scale interval [e] (ct) 0,01 ct Display Display type OLED Display digit height 12 mm Display backlight LED is self-luminous Languages of the user interface German English Construction Dimension housing (W×D×H) 213×433×344 mm Dimensions rectangular draught 166×156×220 mm shield - inner (W×D×H) Dimensions rectangular draught 213×156×225 mm shield - outer (W×D×H) Dimensions weighing surface  $(\emptyset)$ 91 mm Material housing cast aluminium, plastic Material weighing plate stainless steel Material platform Stainless steel Material draught shield glass Levelling feet adjustable 1 **Functions** Number of keys for operation 11 Capacity display 1 Tare function manual (multi) Percentage determination 1 Counting function 1 Tolerance weighing 1 Function for averaging under 1 unstable weighing conditions Recipe weighing - number of 5 database entries RS-232 standard USB-Interfaces Host/Master USB-Device Counting Smallest piece weight when piece 1 mg counting - laboratory conditions Smallest piece weight when piece 10 mg counting - normal conditions

# KERN ABP 200-5AM



Premium analytical balance with the latest Single-Cell Generation for extremely rapid, stable weighing results - now also as a version with automatic sliding doors

Counting reference weight can be entered	✓
Reference quantity	10, 20, 50, 100
Counting resolution (laboratory conditions)	220.000

#### Power Supplay

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 1.6 A
Plug-in power supply type	Power adapter
Supplied plug-in power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

### Environmental conditions

Humity of environment [Max]	80 %	
Ambient temperature [Min]	10 °C	
Ambient temperature [Max]	30 °C	

### Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	382×585×535 mm
Net weight approx.	9 kg
Gross weight approx.	13 kg

#### Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for conformity assessment	965-201
Article number for DAkkS calibration	963-101

## Piktogramme

#### STANDARD



**OPTION** 



FACTORY

