


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:5051102796

Status:Active

Overview:Easy-On FFC FPC Connectors

Description:Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 27 Circuits, 150°C Operating Temperature, Gold over Nickel Plating



Documents:	
3D Model	Datasheet (PDF)
Drawing (PDF)	Product Guide (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5051100008-PS-000 (PDF)	Reference Guide (PDF)
Packaging Specification 5051109200-200 (PDF)	

General	
Product Family	FFC/FPC Connectors
Series	505110
Comments	Black Actuator
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	FD19
Taxonomy	FFC / FPC Connectors
UPC	191128824088
Physical	
Actuator Type	Front Flip
Circuits (Loaded)	27
Color - Resin	Beige
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	1.90mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	219.700/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.051µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

505110 Series

Packaging Specification
Product Specification
Sales Drawing

5051109200-200
5051100008-PS-000
5051100008-SD-000, 5051101008-SD-000

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION