

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5047543520

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.30mm Pitch Easy-On Back Flip FPC Connector, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 35 Circuits



Documents:	
Drawing (PDF)	Application Specification AS-504754-002-001 (PDF)
3D Model	Packaging Specification 5047549200-200 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-504754-002-001 (PDF)	

General	
Product Family	FFC/FPC Connectors
Series	504754
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Taxonomy	FFC / FPC Connectors
UPC	889056000277
Physical	
Actuator Type	Back Flip
Circuits (Loaded)	35
Circuits (maximum)	35
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	10
Mated Height	0.75mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	42.547/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.30mm
Pitch - Termination Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only
Electrical	
Current - Maximum per Contact	0.3A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-504754-002-001
Packaging Specification	5047549200-200
Product Specification	PS-504754-002-001
Sales Drawing	SD-504754-003-001, SD-504754-004-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

504754 Series

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION