

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5047540700

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.30mm Pitch Easy-On Back Flip FPC Connector with Lock Terminal, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 7 Circuits



Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification 5047540000-000 (PDF)

Application Specification AS-504754-002-001 (PDF)

Packaging Specification 5047549200-200 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	FFC/FPC Connectors
Series	504754
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Taxonomy	FFC / FPC Connectors
UPC	889056000123
Physical	
Actuator Type	Back Flip
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	10
Mated Height	0.75mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	13.567/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.30mm
Pitch - Termination Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only
Electrical	
Current - Maximum per Contact	0.3A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-504754-002-001
Packaging Specification	5047549200-200
Product Specification	5047540000-000
Sales Drawing	5047540000-000, 5047541000-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

504754 Series

Mates With

Premo-Flex FPC Jumper with Notches

15031

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION