

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2026560021

Status:

Active

Overview:

Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems

Description:

1.20mm Pitch, Pico-EZmate Slim PCB Header, Single Row, Vertical, Friction Lock, 2 Circuits



Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification 2026540000-000 (PDF)

Application Specification 2026540000-A00 (PDF)

Packaging Specification 2026569200-200 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	202656
Application	Signal, Wire-to-Board
Overview	Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems
Product Name	Pico-EZmate Slim
Taxonomy	PCB Headers and Receptacles
UPC	191128201674
Physical	
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	1.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	22.640/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.20mm
Pitch - Termination Interface	1.20mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-25° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	2.5A
Voltage - Maximum	50V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

202656 Series

Mates With

Pico-EZmate Slim Receptacle Housing 202654

Material Info

Reference - Drawing Numbers

Application Specification	2026540000-A00
Packaging Specification	2026569200-200
Product Specification	2026540000-000
Sales Drawing	2026560000-000, 2026560001-000

This document was generated on 10/19/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION