

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757571431

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Dual Row Header, Vertical, 6 Circuits, 1.5µm Tin (Sn) Plating, 11.20mm Mating Pin Length, 3.05mm PC Tail Length

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-75757-000-001 (PDF)

Packaging Specification PK-36518-340-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Headers

75757

Power, Wire-to-Board

3.50 x 6.00mm dual row grid

PCB Header

MX150 Connector System

MX150

PCB Headers and Receptacles

822350702270

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to Mating Part

Polarized to PCB

Shrouded

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

6

6

Black

25

No

No

No

None

None

Brass

Tin

Tin

High Temperature Thermoplastic

1.452/g

2

Vertical

3.05mm

No

None

1.57mm

Tube

3.50mm

3.50mm

1.524µm

No

No

No

Yes

-40° to +125°C

Through Hole

Electrical

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75757 Series

Mates With

33472 Dual Row MX150 Receptacles

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	015
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-340-001
Product Specification	PS-75757-000-001
Sales Drawing	SD-75757-002-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION