

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1511050004

Status:

Active

Overview:

MiniDIMM Sockets

Description:

0.50mm Pitch DDR4 miniDIMM Socket, Surface Mount, Vertical, with Natural (Off-White) Latches, without Center Forklock, without Pick and Place Cap, 288 Circuits



Documents:

Drawing (PDF)

Product Specification PS-151105-0001-001 (PDF)

Application Specification AS-151105-0001-001 (PDF)

Application Specification AS-151105-0002-001 (PDF)

Packaging Specification PK-151105-0001-000 (PDF)

Test Summary TS-151105-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Memory Module Sockets
Series	151105
Component Type	Socket
JEDEC Outline	MO-314
Overview	MiniDIMM Sockets
Product Name	DDR4 MiniDIMM
Taxonomy	Memory Module Connectors
UPC	889056426541
Physical	
Circuits (Loaded)	288
Circuits (maximum)	288
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Housing Color	Black
Keying to Mating Part	None
Latch Color	Natural (Off-White)
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	3.810/g
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.75A
Voltage - Maximum	29V AC (RMS)/DC
Voltage Key	1.2V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	REFLOW

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

151105 Series

Mates With

JEDEC MO-314 Memory Modules

Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-151105-0001-001, AS-151105-0002-001
Electrical Model Document	EE-151105-0001-001
Packaging Specification	PK-151105-0001-000
Product Specification	PS-151105-0001-001
S-Parameter Model	SP-151105-0001-001
Sales Drawing	SD-151105-0001-000
Signal Integrity Report	SI-151105-0001-001
Test Summary	TS-151105-0001-001

This document was generated on 02/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION