

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0439151213

Status:

Active

Overview:

Mini-Fit Sr. Power Connectors

Description:

10.00mm Pitch Mini-Fit Sr. Header, Dual Row, Vertical, 3.18mm PCB Thickness, 0.76µm Gold (Au) Selective Plating, 10 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	43915
Application	Power, Wire-to-Board
Component Type	PCB Header
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
Taxonomy	PCB Headers and Receptacles
UPC	800756521367

Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	22.534/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	5.10mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	10.00mm
Pitch - Termination Interface	10.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

43915 Series

Mates With

Mini-Fit Sr. Receptacle Housing 43914

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	50.0A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	235
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-43915-001-001, SD-43915-002-001

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION