

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757103006

Status:

Active

Overview:

Description:

GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Left Guide, 11 Rows, 6 Columns, 132 Circuits, Lead-Free

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	75710
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Data Rate	12.0 Gbps
Overview	gbx_itrac_backplane_connector_system
Product Name	GbX I-Trac
Taxonomy	Backplane Connectors
UPC	822350316859
Physical	
Circuits (Loaded)	132
Circuits (maximum)	132
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	20.600/g
Number of Columns	6
Number of Pairs	Open Pin Field
Number of Rows	11
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +80°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	1.0A
Shield Type	N/A
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75710 Series

Mates With

75705 GbX I-Trac Vertical Header Module.

75910 GbX I-Trac Right Angle Header Module

Use With

78234 GbX I-Trac Right Angle Power Header.

76153 Pirate Cannon Wide Guide Module

Solder Process Data

Lead-freeProcess CapabilityN/A

Material Info

Reference - Drawing Numbers

Packaging SpecificationPK-70873-609-001
Product SpecificationPS-45499-002-001, PS-75710-999-001
Sales DrawingSD-75710-002-001

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION