

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1726722008

Status:

Active

Overview:

Super Sabre Connector System

Description:

7.50mm Pitch Super Sabre Receptacle Crimp Housing, UL 94V-0, 8 Circuits

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-171825-001-001 (PDF)

Packaging Specification PK-44441-001-001 (PDF)

Test Summary TS-171825-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

172672

Power, Wire-to-Board, Wire-to-Wire

Super Sabre Connector System

Super Sabre

Connector Housings

889056025843

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

8

Black

94V-0, 94V-2

Receptacle

No

Yes

Yes

Nylon

6.064/g

1

Carton

No

7.50mm

Yes

No

-40° to +125°C

Electrical

Current - Maximum per Contact

34.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

Test Summary

PK-44441-001-001

PS-171825-001-001

1726720000-SD-000

TS-171825-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

172672 Series

Mates With

Super Sabre Vertical Header 172042 .

Super Sabre Right Angle Header 172043 .

Super Sabre Plug Housing 172673 , 43680

Use With

171825 Super Sabre Female Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION