

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1713351807](#)
Status: **Active**
Overview: [Impel and Impel Plus Backplane Solutions](#)
Description: Impel 90 Ohm, 3 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Open Endwalls, 8 Columns, 48 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm

Documents:	
3D Model (PDF)	Application Specification AS-171320-991-001 (PDF)
Drawing (PDF)	Application Specification AS-171320-992-001 (PDF)
3D Model	Packaging Specification 1713351807-PK-000 (PDF)
Product Specification PS-171320-999-001 (PDF)	Symbol Footprint Data SYM-171335-1807-001 (PDF)
Application Specification 1713209994-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-171320-990-001 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	171335
Application	Backplane
Component Type	PCB Header
Data Rate	40.0 Gbps
Overview	Impel and Impel Plus Backplane Solutions
Product Name	Impel
Taxonomy	Backplane Connectors
UPC	887191240282
Physical	
Circuits (Loaded)	48
Circuits (maximum)	48
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Nickel, Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.512/g
Number of Columns	8
Number of Pairs	3
Number of Rows	6
Orientation	Vertical
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C

Electrical



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[171335 Series](#)

Mates With
[Impel Right-Angle Daughtercard 1719901038](#)

Current - Maximum per Contact	0.75A
Impedance	90Ω
Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	1713209994-AS-000, AS-171320-990-001, AS-171320-991-001, AS-171320-992-001
Electrical Model Document	1719900001-000, 1727301117-000
Packaging Specification	1713351807-PK-000
Product Specification	PS-171320-999-001
S-Parameter Model	1719900001-000, 1727301117-000
Sales Drawing	SD-171335-0001-001
Symbol/Footprint Data	SYM-171335-1807-001

This document was generated on 12/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION