

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0878331420

Status:

Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Right-Angle, Through Hole, 14 Circuits, 0.38µm Gold (Au) Plating, without PCB Locator, with Locking Windows, Center Polarization Slot, Tube

|                                                              |                                                                |
|--------------------------------------------------------------|----------------------------------------------------------------|
| Documents:                                                   |                                                                |
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Packaging Specification PK-87831-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Packaging Specification PK-87831-002-001 (PDF)</a> |
| <a href="#">3D Model</a>                                     | <a href="#">Packaging Specification PK-87831-300-001 (PDF)</a> |
| <a href="#">Product Specification PS-87831-027-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |

Agency Certification


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

General

|                |                                                      |
|----------------|------------------------------------------------------|
| Product Family | PCB Headers                                          |
| Series         | 87833                                                |
| Application    | Signal, Wire-to-Board                                |
| Comments       | Contact Molex for application in automotive industry |
| Component Type | PCB Header                                           |
| Overview       | Milli-Grid Connector System                          |
| Product Name   | Milli-Grid                                           |
| Taxonomy       | PCB Headers and Receptacles                          |
| UPC            | 822348189120                                         |

Physical

|                                |                 |
|--------------------------------|-----------------|
| Breakaway                      | No              |
| Circuits (Loaded)              | 14              |
| Circuits (maximum)             | 14              |
| Color - Resin                  | Black           |
| Durability (mating cycles max) | 100             |
| First Mate / Last Break        | No              |
| Flammability                   | 94V-0           |
| Glow-Wire Capable              | No              |
| Guide to Mating Part           | No              |
| Keying to Mating Part          | None            |
| Lock to Mating Part            | Yes             |
| Material - Metal               | Phosphor Bronze |
| Material - Plating Mating      | Gold            |
| Material - Plating Termination | Tin             |
| Material - Resin               | Nylon           |
| Net Weight                     | 0.812/g         |
| Number of Rows                 | 2               |
| Orientation                    | Right Angle     |
| PC Tail Length                 | 2.16mm          |
| PCB Locator                    | No              |
| PCB Retention                  | None            |
| PCB Thickness - Recommended    | 1.60mm          |
| Packaging Type                 | Tube            |
| Pitch - Mating Interface       | 2.00mm          |
| Pitch - Termination Interface  | 2.00mm          |
| Plating min - Mating           | 0.381µm         |
| Plating min - Termination      | 1.905µm         |
| Polarized to PCB               | No              |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

87833 Series

Mates With

Milli-Grid Vertical Through Hole Receptacle [79107](#) , [78787](#) , Milli-Grid Flex-to-Board Vertical Receptacle [79108](#) , Milli-Grid Vertical Surface Mount Receptacle [79109](#) , [78788](#) , Milli-Grid Crimp Housing [51110](#) , Milli-Grid Cable-to-Board Receptacle [87568](#)

|                                                |                                                         |
|------------------------------------------------|---------------------------------------------------------|
| Shrouded                                       | Fully                                                   |
| Stackable                                      | No                                                      |
| Surface Mount Compatible (SMC)                 | Yes                                                     |
| Temperature Range - Operating                  | -55° to +105°C                                          |
| Termination Interface: Style                   | Through Hole                                            |
| <b>Electrical</b>                              |                                                         |
| Current - Maximum per Contact                  | 2.0A                                                    |
| Voltage - Maximum                              | 125V                                                    |
| <b>Solder Process Data</b>                     |                                                         |
| Duration at Max. Process Temperature (seconds) | 011                                                     |
| Lead-freeProcess Capability                    | SMC&WAVE                                                |
| Max. Cycles at Max. Process Temperature        | 001                                                     |
| Process Temperature max. C                     | 265                                                     |
| <b>Material Info</b>                           |                                                         |
| Engineering Number                             | NT501-4834                                              |
| <b>Reference - Drawing Numbers</b>             |                                                         |
| Packaging Specification                        | PK-87831-001-001, PK-87831-002-001,<br>PK-87831-300-001 |
| Product Specification                          | PS-87831-027-001                                        |
| Sales Drawing                                  | SD-87833-0001-001                                       |

This document was generated on 01/25/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**