


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0015913164
Status:	Active
Overview:	SL Modular Connectors
Description:	2.54mm Pitch SL Wire-to-Board Header, Low Profile, Surface Mount, Single Row, Right-Angle, 3.05mm Pocket, Shrouded, with Press-fit Plastic Peg, 16 Circuits, Tin (Sn) Plating
Replacement Part Number :	http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=17197700161719770016 (drop-in)



Series image - Reference only

Documents:	
Drawing (PDF)	Product Specification PS-70541-001 (PDF)
3D Model	Packaging Specification PK-70873-016-001 (PDF)
3D Model (PDF)	Test Summary TS-70541-100-001 (PDF)
Product Specification PS-70400-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	70634
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	SL Modular Connectors
Product Name	SL
Replacement Part Number	1719770016 (drop-in)
Taxonomy	PCB Headers and Receptacles
UPC	800753772458
Physical	
Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.635/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70634 Series

Mates With

SL Crimp Housing 70066 Option N, 70066 Option G, 70066 Option A, 70430 Option G, 70400 Option G

Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	REFLOW
Process Temperature max. C	260
Material Info	
Engineering Number	70634-0015
Reference - Drawing Numbers	
Packaging Specification	PK-70873-016-001
Product Specification	PS-70400-001, PS-70541-001
Sales Drawing	706340000-SD-000
Test Summary	TS-70541-100-001

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION