

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901471132

Status:

Active

Overview:

C-Grid Connector Products

Description:


C-Grid III PC Board Connector, Single Row, Vertical, 32 Circuits, Tin (Sn) Plating

Documents:	
3D Model	Application Specification 713080001-AS-000 (PDF)
Drawing (PDF)	Application Specification 901190001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-90147-001-002 (PDF)
Product Specification PS-99020-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
General	
Product Family	PCB Receptacles
Series	90147
Application	Board-to-Board, Signal
Component Type	PCB Receptacle
Overview	C-Grid Connector Products
Product Name	C-Grid III
Taxonomy	PCB Headers and Receptacles
UPC	800753674905

Physical	
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2.750/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	3.0A
Grounding to PCB	No



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
90147 Series

Mates With
C-Grid III Vertical Header 90120 . C-Grid III Right-Angle Header 90121

Use With
90120 , 90121

Voltage - Maximum

350V

Material Info

Reference - Drawing Numbers

Application Specification

713080001-AS-000, 901190001-AS-000

Packaging Specification

PK-90147-001-002

Product Specification

PS-99020-0001-001

Sales Drawing

SDA-90147-001

This document was generated on 02/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION