

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0459110025

Status:


Active

Overview:

Edge Card Connectors

Description:

EXTreme PowerEdge Mixed Power/Signal Card Edge Connector, Double Sided, 4 Segments or 3.18mm Thick PC Board



Series image - Reference only

Documents:

[3D Model](#)

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[Product Specification PS-45719-001-001 \(PDF\)](#)

[Packaging Specification PK-45714-001-001 \(PDF\)](#)

[Test Summary TS-45844-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Edge Card Connectors
Series	45911
Component Type	Edgecard to PCB
Data Rate	Unrated
Edge Card Thickness	1.57mm
High Power Bay (30.0A or more)	Yes
Orientation	Vertical
Overview	Edge Card Connectors
Product Name	EXTreme PowerEdge
Standard Based	General
Taxonomy	Card Edge Connectors
UPC	822350709576

Physical	
(p)ower-(s)ignal Configuration	2p - 2p - 2p - 8s
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	250
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	N/A
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.164/g
PC Tail Length	4.50mm
PCB Thickness - Recommended	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	12.90mm
Plating min - Mating	0.762µm
Plating min - Termination	3.810µm
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	3.0A, 40.0A
Voltage - Maximum	250V

EU ELV
Not Relevant

<u>EU RoHS</u> Compliant	<u>China RoHS</u>
<u>REACH SVHC</u> Not Contained Per - D(2022)4187-DC (10 June 2022)	
<u>Halogen-Free</u> Status Low-Halogen	

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
45911 Series

Mates With
1.58mm Double Sided Card Edge

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-45714-001-001
Product Specification	PS-45719-001-001
Sales Drawing	SD-45911-001-001, SD-45911-002-001
Test Summary	TS-45844-001-001

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION