

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1713201038](#)
Status: **Active**
Overview: [Impel and Impel Plus Backplane Solutions](#)
Description: Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 8 Columns, 64 Circuits, Plated Through Hole Dimension 0.36mm

Documents:	
3D Model	Application Specification AS-171320-991-001 (PDF)
3D Model (PDF)	Application Specification AS-171320-992-001 (PDF)
Drawing (PDF)	Packaging Specification PK-78888-085-001 (PDF)
Product Specification PS-171320-999-001 (PDF)	Symbol Footprint Data SYM-171320-1038-001 (PDF)
Application Specification 1713209994-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-171320-990-001 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	171320
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Data Rate	40.0 Gbps
Overview	Impel and Impel Plus Backplane Solutions
Product Name	Impel
Taxonomy	Backplane Connectors
UPC	887191302539
Physical	
Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	18.709/g
Number of Columns	8
Number of Pairs	4
Number of Rows	8
Orientation	Right Angle
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C
Electrical	
Current - Maximum per Contact	0.75A



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[171320 Series](#)

Mates With
Impel Vertical Backplane Header
[1713151804](#) , [1713151805](#) , [1713151807](#) ,
[1713151808](#) , [1713151817](#) , [1713151828](#) ,
[1713151837](#)

Impedance	90Ω
Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	1713209994-AS-000, AS-171320-990-001, AS-171320-991-001, AS-171320-992-001
Electrical Model Document	1713201218-000, 1713202061REVA-000
Packaging Specification	PK-78888-085-001
Product Specification	PS-171320-999-001
S-Parameter Model	1713201218-000, 1713202061-000
Sales Drawing	SD-171320-0001-001
Symbol/Footprint Data	SYM-171320-1038-001

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION