

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901301238

Status:


Active

Overview:

C-Grid III Interconnects

Description:

C-Grid III Header, Dual Row, Vertical, Shrouded, Fully Loaded, 38 Circuits, Black, 0.38µm Gold (Au) Selective Plating



Documents:	
3D Model	Application Specification 901190001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-90130-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-91814-005-001 (PDF)
Product Specification PS-99020-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	90130
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	C-Grid III Interconnects
Product Name	C-Grid III
Taxonomy	PCB Headers and Receptacles
UPC	800753698130

Physical	
Breakaway	No
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	4.074/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Closed Ends

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90130 Series

Mates With

C-Grid III Crimp Housing 90142 , 90143

Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	350V AC/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Reference - Drawing Numbers	
Application Specification	901190001-AS-000
Packaging Specification	PK-90130-001-001, PK-91814-005-001
Product Specification	PS-99020-0001-001
Sales Drawing	SDA-90130-001

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION