

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0761559107](#)
Status: **Active**
Overview: Impact Backplane Connector and Cable Assembly System
Description: Impact 100 Ohm 4 Pair Vertical Backplane Header, Right Guided, Left Endwall, 10 Columns, 120 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free

Documents:

| | |
|--|---|
| 3D Model | Application Specification AS-76060-994-001 (PDF) |
| 3D Model (PDF) | Application Specification AS-76060-9999-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-70873-757-001 (PDF) |
| Product Specification PS-45499-002-001 (PDF) | Test Summary TS-76160-0001-001 (PDF) |
| Product Specification PS-76060-999-001 (PDF) | Symbol Footprint Data SYM-76155-9107-001 (PDF) |
| Application Specification AS-76060-990-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification


UL E29179

General

| | |
|-------------------------------|--|
| Product Family | Backplane Connectors |
| Series | 76155 |
| Application | Conventional |
| Application Tooling Documents | TM-622018799-001 |
| Component Type | PCB Header |
| Data Rate | 25.0 Gbps |
| Overview | Impact Backplane Connector and Cable Assembly System |
| Product Name | Impact |
| Taxonomy | Backplane Connectors |
| UPC | 800756923970 |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 120 |
| Circuits (maximum) | 120 |
| Color - Resin | Black |
| Durability (mating cycles max) | 200 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Guide to Mating Part | Yes |
| Keying to Mating Part | None |
| Material - Metal | High Performance Alloy (HPA) |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 6.120/g |
| Number of Columns | 10 |
| Number of Pairs | 4 |
| Number of Rows | 12 |
| Orientation | Vertical |
| PC Tail Length | 1.40mm |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.00mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 1.90mm |
| Pitch - Termination Interface | 1.90mm |
| Plating min - Mating | 0.762µm |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76155 Series](#)

Mates With

[76160 Impact 100 Ohm Daughtercard](#)

| | |
|-------------------------------|------------------------------|
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -55° to +85°C |
| Termination Interface: Style | Through Hole - Compliant Pin |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.75A |
| Impedance | 100Ω |
| Shield Type | N/A |
| Shielded | No |
| Voltage - Maximum | 30V AC (RMS)/DC |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info**Reference - Drawing Numbers**

| | |
|---------------------------|--|
| Application Specification | AS-76060-990-001, AS-76060-994-001, AS-76060-9999-001 |
| Packaging Specification | PK-70873-757-001 |
| Product Specification | PS-45499-002-001, PS-76060-999-001 |
| Sales Drawing | SD-76155-003-001 |
| Symbol/Footprint Data | SYM-76155-9107-001 |
| Test Summary | TS-76160-0001-001 |

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION