

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2132741003

Status:

Active

Overview:

PowerPlane Busbar Power Connectors and Cable Assemblies

Description:

PowerPlane Bus Bar Assembly, Vertical Mount, Dual Hole, Closed Side Walls, Silver (Ag) Plated



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[Product Specification 2132740001-PS-000 \(PDF\)](#)

[Application Specification 2132740001-AS-000 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	PCB Receptacles
Series	213274
Application	Power
Component Type	PCB Receptacle
Overview	PowerPlane Busbar Power Connectors and Cable Assemblies
Product Name	PowerPlane
Taxonomy	PCB Headers and Receptacles
UPC	195842284487
Physical	
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Nickel
Material - Resin	Polyester
Net Weight	19.824/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Screw
Electrical	
Current - Maximum per Contact	320.0A
Voltage - Maximum	600V AC
Material Info	
Reference - Drawing Numbers	
Application Specification	2132740001-AS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

213274 Series

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION