

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2166231022

Status:

Active

Overview:

Squba Sealed Wire-to-Wire Connectors

Description:

Squba 3.6 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 300.00mm Length, Tin (Sn) Plating, 2 Circuits, Black



Documents:

[3D Model](#)

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	216623
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Squba-to-Pigtail
Overmolded	No
Overview	Squba Sealed Wire-to-Wire Connectors
Product Name	Squba
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264746606
Physical	
Cable Length	300.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	13.152/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm-2.40mm
Wire Size AWG	16
Wire/Cable Type	UL 11028
Electrical	
Current - Maximum per Contact	14.0A
Voltage - Maximum	600V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2166231021-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

216623 Series

Mates With

Squba 3.6 Receptacle Assembly

2077820002

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION