

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026613080

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 396 Header, Right-Angle, without Peg, 8 Circuits, Gold (Au) Plating

Documents:

- 3D Model

Packaging Specification 417720000-PK-000 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-26-60-3080-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

41772

Application

Board-to-Board, Power, Wire-to-Board

Component Type

PCB Header

Overview

KK Interconnect Systems

Product Name

KK 396

Taxonomy

PCB Headers and Receptacles

UPC

800754202794

Physical

Breakaway

No

Circuits (Loaded)

8

Circuits (maximum)

8

Color - Resin

Natural

Durability (mating cycles max)

100

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Matte Tin

Material - Resin

Polyester

Net Weight

2.880/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.56mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Plating min - Mating

0.508µm

Plating min - Termination

0.508µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Partial

Stackable

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41772 Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	41772-0025
Reference - Drawing Numbers	
Packaging Specification	417720000-PK-000
Product Specification	PS-08-50-001
Sales Drawing	SDA-41772-000, SDA-41772-002
Symbol/Footprint Data	SYM-26-60-3080-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION