

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022051152

Status:

Active

Overview:

Mini-Latch Wire-to-Board / Wire-to-Wire Connector System

Description:

Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 15 Circuits, Tin (Sn) Plating, Natural

Documents:

3D Model	Application Specification 511910000-AS-000 (PDF)
3D Model (PDF)	Application Specification 511910000-AS-001 (PDF)
Drawing (PDF)	Packaging Specification 50469200-SPK-200 (PDF)
Product Specification 50510002-PS-000 (PDF)	Packaging Specification SPK-5046-001-001 (PDF)
Product Specification 511910000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family	PCB Headers
Series	5046
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
Product Name	KK, Mini-Latch
Taxonomy	PCB Headers and Receptacles
UPC	800753591042

Physical

Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1951.500/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5046 Series

Mates With

2.50mm Pitch Housing [51191](#)

Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5046-15A
Reference - Drawing Numbers	
Application Specification	511910000-AS-000, 511910000-AS-001
Packaging Specification	50469200-SPK-200, SPK-5046-001-001
Product Specification	50510002-PS-000, 511910000-PS-000
Sales Drawing	50460002-000

This document was generated on 02/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION