

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0714362164

Status:


Active

Overview:

1.00mm Mezzanine (IEEE 1386)

Description:

1.00mm Mezz (IEEE 1386) Plug, Surface Mount, Dual Row, Vertical Stacking, 64 Circuits, 8.35mm Unmated Height, with PCB Locator Pegs, without Robotic Placement Metal Cap, 0.76µm Gold (Au) Selective Plating, Tube



Documents:	
3D Model	Packaging Specification PK-70873-0607-001 (PDF)
Drawing (PDF)	Packaging Specification PK-70873-063-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-71436-9999-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	71436
Application	Board-to-Board, Signal
Component Type	PCB Header
Overview	1.00mm Mezzanine (IEEE 1386)
Product Name	1.00mm Mezzanine (IEEE 1386)
Taxonomy	Board-to-Board Connectors
UPC	800753677814
Physical	
Breakaway	No
Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Natural
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Mated Height	10.00mm, 12.00mm, 13.00mm, 15.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.402/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tube
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Surface Mount
Electrical	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

71436 Series

Mates With

71439 1.00mm Mezz (IEEE 1386) Receptacle. Be sure to match like stack heights

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-0607-001, PK-70873-063-001
Product Specification	PS-71436-9999-001
Sales Drawing	714362000-000

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION