

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347072030

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 2 Bay Vertical Headers, 20 Circuits, Bay A 10 Circuit Power Header, Polarization B, Gray; Bay B 10 Circuit Power Header, Polarization A, Black, Tray



Series image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [3D Model \(PDF\)](#)
- [Product Specification PS-31372-100-001 \(PDF\)](#)
- [Application Specification AS-34729-020-001 \(PDF\)](#)
- [Brochure \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	34707
Application	Automotive, Power, Wire-to-Board
Comments	Bay A 10 Circuits Stac64 Vertical Power Header, Polarization B; Bay B 10 Circuits Stac64 Vertical Power Header, Polarization A
Component Type	PCB Header
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
Taxonomy	PCB Headers and Receptacles
UPC	883906551407

Physical

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black, Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	17.104/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.36mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.30mm, 3.50mm, 5.25mm
Pitch - Termination Interface	2.30mm, 3.50mm, 5.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34707 Series

Mates With

31408 USCAR 2.54mm (.100") Pitch
Receptacle, 31372 5.25mm (.206") Pitch
Hybrid Receptacle Assembly, 34729
2.54mm (.100") Pitch Stac64 Right Angle
Receptacle

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	500V

Solder Process Data

Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-34729-020-001
Product Specification	PS-31372-100-001
Sales Drawing	SD-34707-200-001

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION