

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0367831201

Status:

Active

Overview:

MX120G Sealed Connectors

Description:

MX120G Sealed Header Connector Assembly, 12 Circuit, Color Mark Identification
Black

Documents:

3D Model	Product Specification PS-36783-001-001 (PDF)
Drawing (PDF)	Application Specification AS-36783-001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	36783
Application	Wire-to-Board
Component Type	PCB Header
Overview	MX120G Sealed Connectors
Product Name	MX120G
Taxonomy	PCB Headers and Receptacles
UPC	887191147673

Physical

(p)ower-(s)ignal Configuration	12p - 0s
Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94HB
Glow-Wire Capable	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	8.357/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	3.20mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

36783 Series

Mates With

367921201 3.20mm MX120G Pitch Sealed
Female Connector Assembly

Current - Maximum per Contact	10.5A
Voltage - Maximum	28V DC
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-36783-001-001
Product Specification	PS-36783-001-001
Sales Drawing	SD-36783-004-001

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION