

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050362426

Status:


Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Jr. Header, Dual Row, Right-Angle, with PCB Mounting Peg, 16 Circuits, LCP Housing, 94V-0, Matte Tin (Sn), Glow-Wire Capable



Documents:	
Drawing (PDF)	Product Specification PS-5556-001-001 (PDF)
3D Model	Product Specification PS-5556-004-001 (PDF)
3D Model (PDF)	Packaging Specification PK-5569-003-001 (PDF)
Product Specification 55560004-PS-CH-000 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification 55560004-PS-ES-000 (PDF)	Test Summary TS-5569-001-001 (PDF)
Product Specification 55560004-PS-SK-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-45750-001-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	5569
Application	Power, Wire-to-Board
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire. See Molex Product specification PS-5556-001 for additional current de-rating information.
Component Type	PCB Header
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
Taxonomy	PCB Headers and Receptacles
UPC	883906713324
Physical	
Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.730/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.78mm

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[5569](#) Series

Mates With

Mini-Fit TPA2 Receptacle Housing [172708](#)

Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Plating min - Mating	2.540μm
Plating min - Termination	2.540μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	255
Material Info	
Engineering Number	5569-16A7MS-130-T
Reference - Drawing Numbers	
Packaging Specification	PK-5569-003-001
Product Specification	55560004-PS-CH-000, 55560004-PS-ES-000, 55560004-PS-SK-000, PS-45750-001-001, PS-5556-001-001, PS-5556-004-001
Sales Drawing	55690007-SD-000
Test Summary	TS-5556-002-001, TS-5569-001-001

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION