

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192130008](#)  
**Status:** **Active**  
**Overview:** [Wire Pins](#)  
**Description:** Avikrimp Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">Drawing (PDF)</a>  | <a href="#">Product Specification PS-19902-011-001 (PDF)</a> |
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-19902-015-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

**General**

|                         |                                   |
|-------------------------|-----------------------------------|
| Product Family          | Crimp Terminals                   |
| Series                  | <a href="#">19213</a>             |
| Application             | Power, Wire-to-Component          |
| Comments                | Pin Length 11.68mm                |
| Crimp Quality Equipment | Yes                               |
| Overview                | <a href="#">Wire Pins</a>         |
| Packaging Alternative   | <a href="#">192130007 (Loose)</a> |
| Product Name            | Wire Pin                          |
| Taxonomy                | Crimp Terminals                   |
| UPC                     | 800753053489                      |

**Physical**

|                              |                       |
|------------------------------|-----------------------|
| Flammability                 | 94V-2                 |
| Gender                       | Male                  |
| Material - Metal             | Copper                |
| Material - Plating Mating    | Tin                   |
| Net Weight                   | 2.203/g               |
| Packaging Type               | Adhesive Tape on Reel |
| Plating min - Mating         | 1.016µm               |
| Termination Interface: Style | Crimp or Compression  |
| Wire Insulation Diameter     | 6.35mm max.           |
| Wire Size AWG                | 10, 12                |
| Wire Size mm <sup>2</sup>    | N/A                   |

**Material Info**

|                    |          |
|--------------------|----------|
| Engineering Number | WP-8210T |
|--------------------|----------|

**Reference - Drawing Numbers**

|                       |                                    |
|-----------------------|------------------------------------|
| Product Specification | PS-19902-011-001, PS-19902-015-001 |
| Sales Drawing         | SD-19213-002-001                   |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19213 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

|  |                           |
|--|---------------------------|
| ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press | <a href="#">192880179</a> |
| Mini-Mac Pneumatic Applicator for Industrial Terminals 6-26 AWG  | <a href="#">638851500</a> |