

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022051132

Status:


Active

Overview:

Mini-Latch Wire-to-Board / Wire-to-Wire Connector System

Description:

Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 13 Circuits, Tin (Sn) Plating, Natural



Series image - Reference only

Documents:	
3D Model	Application Specification 511910000-AS-000 (PDF)
3D Model (PDF)	Application Specification 511910000-AS-001 (PDF)
Drawing (PDF)	Packaging Specification 50469200-SPK-200 (PDF)
Product Specification 50510002-PS-000 (PDF)	Packaging Specification SPK-5046-001-001 (PDF)
Product Specification 511910000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	5046
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
Product Name	KK, Mini-Latch
Taxonomy	PCB Headers and Receptacles
UPC	800753739857
Physical	
Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1687.300/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5046 Series

Mates With

2.50mm Pitch Housing 51191

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No
No
-40° to +105°C
Through Hole

Electrical

Current - Maximum per Contact

Voltage - Maximum

3.0A
250V

Material Info

Engineering Number

5046-13A

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

511910000-AS-000, 511910000-AS-001
50469200-SPK-200, SPK-5046-001-001
50510002-PS-000, 511910000-PS-000
50460002-000

This document was generated on 01/30/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION