

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348050113

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

CTX150 Female Terminal, Tin (Sn), 14-16 AWG D-Wind, Left Payoff, Grip Code L



Series image - Reference only

- Documents:
- Drawing (PDF)

Product Specification PS-502307-001-001 (PDF)

Application Specification AS-502307-001-001 (PDF)

Application Specification AS-502307-001-CH-001 (PDF)

Application Specification AS-502307-001-FR-001 (PDF)

Application Specification AS-560065-001-001 (PDF)

Application Specification AS-560065-001-CH-001 (PDF)

Application Specification AS-560065-001-FR-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Name

Taxonomy

UPC

Crimp Terminals

34805

Power, Wire-to-Wire

Yes

CMC and CMX Sealed, Hybrid, Modular Connectors

CTX150

Crimp Terminals

884982651203

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

10

Female

Copper Alloy

Tin

Nickel

0.267/g

Reel

Crimp or Compression

2.80mm

14, 16

1.50-2.00

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

250V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

AS-502307-001-001, AS-502307-001-CH-001, AS-502307-001-FR-001, AS-560065-001-001, AS-560065-001-CH-001, AS-560065-001-FR-001

PS-502307-001-001

SD-34805-001-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34805 Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for CTX 1.50mm Receptacle Terminal, 1.25, 1.50, and 2.00mm²	638194100
FineAdjust Applicator for CTX150 Receptacle Terminals, 1.25mm², 1.50mm² & 2.00mm²	639010600

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION