

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640018

Status:

Active

Overview:

Perma-Seal Terminals

Description:

Perma-Seal Female Quick Disconnect Receptacle for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-015-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19164

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Perma-Seal Terminals

Product Name

Perma-Seal

Taxonomy

Quick Disconnects

Type

Quick Disconnect

UPC

800753113060

Physical

Barrel Type

Closed

Color - Resin

Red

Gender

Female

Glow-Wire Capable

No

Insulation

NiAc

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

1.733/g

Orientation

Straight

Packaging Type

Adhesive Tape on Reel

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

-55° to +125°C

Wire Insulation Diameter

4.32mm max.

Wire Size AWG

18, 20, 22

Electrical

Voltage - Maximum

600V

Material Info

Engineering Number

SAA-9261T

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-015-001

Sales Drawing

SD-19164-020-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880095

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION