

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2451300630

Status:


Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin (Sn) Plating, 3.0m Length, 6 Circuits, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	245130
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	Yes
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
Taxonomy	Power and Signal Cable Assembl
Type	Overmolded Assembly
UPC	191128813891
Physical	
Cable Length	3.0m
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	191.820/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.20mm
Wire Size AWG	20
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	250V AC/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	4000071378-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

245130 Series

Mates With

Nano-Fit Vertical Through Hole Headers [1053101106](#) , [1053121106](#) . Nano-Fit Right-Angle Through Hole Headers [1053141106](#) . Nano-Fit Vertical SMT Headers [1054291106](#) . Nano-Fit Right-Angle SMT Headers [1054051106](#) . Nano-Fit Plug Housing [2014441106](#) , [2014441206](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION