

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194270104

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

5.84mm Pitch MX150L Right-Angle PCB Header, Dual Row, without PCB Flange, Gold (Au) Plated, 10 Circuits



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-19427-001-001 (PDF)
3D Model (PDF)	Brochure (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19427-001-001 (PDF)	

Agency Certification	
UL	E152602
General	
Product Family	PCB Headers
Series	19427
Application	Power, Wire-to-Board
Comments	IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Component Type	PCB Header
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	PCB Headers and Receptacles
UPC	822348740420
Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	24.140/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19427 Series

Mates With

19418 Receptacle Assemblies

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19427-001-001
Product Specification	PS-19427-001-001
Sales Drawing	SD-19427-023-001

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION