

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162921062

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

Standard .093" Male-to-Standard .093" Male Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Natural



Series image - Reference only

Documents:

[3D Model](#)

[3D Model \(PDF\)](#)

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	216292
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Standard 093"-to-Standard 093"
Overmolded	No
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	193264735822
Physical	
Cable Length	300.00mm
Circuits (Loaded)	6
Color - Resin	Natural
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	76.534/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	6.70mm
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size AWG	14
Wire/Cable Type	UL 1015
Electrical	
Current - Maximum per Contact	12.0A
Voltage - Maximum	600V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2162921061-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Not Low-Halogen

Status

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

216292 Series

Mates With

Standard .093" Receptacle Housing [19091066](#) , [19091069](#) . Standard .093" Pin and Socket Header [5219](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION