

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0399200302](#)
Status: **Active**
Overview:
Description: 15.00mm Beau Eurostyle, Fixed Mount PCB Terminal Block, High Voltage, High Power 115A, 2 Circuits

Documents:

[3D Model](#) [Packaging Specification PK-39920-002-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [39920](#)
 Application N/A
 Component Type One Piece
 Overview eurostyle_terminal_blocks
 Product Name Eurostyle Fixed Mount
 Taxonomy Terminal Blocks and Barrier St
 Type Euro Block
 UPC 756054719954


Physical

Circuits (Loaded) 2
 Color - Resin Black
 Entry Angle Horizontal
 Flammability 94V-0
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polyester
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 6.35mm
 PCB Retention Yes
 Panel Mount No
 Pitch - Mating Interface 15.00mm
 Pitch - Termination Interface 15.00mm
 Plating min - Mating 3.810µm
 Plating min - Termination 3.810µm
 Polarized to Mating Part Yes
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating 130°C
 Termination Interface: Style Through Hole
 Wire Size AWG 1, 2, 3, 4, 6, 8
 Wire Size mm² 10.00-35.00

Electrical

Current - Maximum per Contact 115.0A
 Voltage - Maximum 600V

Solder Process Data



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[39920 Series](#)

Lead-freeProcess Capability

WAVE

Material Info

Engineering Number

92B0502

Reference - Drawing Numbers

Packaging Specification

PK-39920-002-001

Sales Drawing

SD-39920-006-001

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION