

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2016060610](#)  
**Status:** **Active**  
**Overview:** High-Current, Universal-Clamp Terminal Blocks  
**Description:** High Current Universal Clamp Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 1 Circuit

**Documents:**

<a href="#">3D Model</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Drawing (PDF)</a>	

**Agency Certification**

UL E48521

**General**

Product Family	Terminal Blocks
Series	<a href="#">201606</a>
Application	Wire-to-Wire
Component Type	One Piece
Overview	<a href="#">High-Current, Universal-Clamp Terminal Blocks</a>
Product Name	Universal Clamp
Taxonomy	Terminal Blocks and Barrier St
Type	Universal Clamp
UPC	78172551120

**Physical**

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Grey
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Number of Rows	1
Orientation	Vertical
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Screw
Wire Size AWG	1/0-6, 6+6, 8+8+8
Wire Size mm <sup>2</sup>	13.00+13.00, 13.00-53.00, 8.30+8.30+8.30

**Electrical**

Current - Maximum per Contact	150.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	MX-KE61
--------------------	---------

**Reference - Drawing Numbers**

Sales Drawing	2016060610-000
---------------	----------------



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[201606 Series](#)

This document was generated on 02/01/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**