

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151360502

Status:


Active

Overview:

MicroClasp Wire-to-Board System

Description:

MicroClasp-to-MicroClasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, 5 Circuits, White



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	15136
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp-to-MicroClasp
Overmolded	No
Overview	MicroClasp Wire-to-Board System
Product Name	MicroClasp
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191128149563
Physical	
Cable Length	150.00mm
Circuits (Loaded)	5
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	4.417/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.28mm
Wire Size AWG	22
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2012341708-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15136 Series

Mates With

MicroClasp Vertical Header 55932

MicroClasp Right Angle Header 55935

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION