

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0480251190

Status:

Active

Overview:

Magnetic Jacks

Description:

Modular Jack, Right-Angle, 10/100, with Integrated Magnetic and LED, 8/8, Lead-Free

- Documents:
- 3D Model (PDF)

Packaging Specification PK-48025-001-001 (PDF)
- Drawing (PDF)

Test Summary TS-48025-009-001 (PDF)
- 3D Model

RoHS Certificate of Compliance (PDF)
- Product Specification PS-48025-005-001 (PDF)

Agency Certification		
CSA		LR19980
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		48025
Comments		With LED
Component Type		PCB Jack
Magnetic		Yes
Overview		Magnetic Jacks
Performance Category		5, 5e
Power over Ethernet (PoE)		Non-PoE
Product Name		Magnetic Jack, RJ45
Taxonomy		Modular Jacks and Plugs
UPC		822350847988
Physical		
Boot Color		N/A
Color - Resin		Black
Durability (mating cycles max)		750
Flammability		94V-0
Inverted / Top Latch		Yes
Jack Height		13.30mm
Keying to Mating Part		Yes
Lightpipes/LEDs		LEDs
Material - Metal		Brass, Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Nylon
Net Weight		7.300/g
Orientation		Right Angle (Side Entry)
PCB Locator		Yes
PCB Retention		Yes
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Port Configuration		1x1
Positions / Loaded Contacts		8/8
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		-40° to +70°C
Termination Interface: Style		Through Hole
Waterproof / Dustproof		No
Wire/Cable Type		N/A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

48025 Series

Mates With

FCC 68 Plugs

Electrical

Current - Maximum per Contact	1.5A
Grounding to PCB	Yes
Grounding to Panel	Panel Ground Tab
Shielded	Yes
Voltage - Maximum	150V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-48025-001-001
Product Specification	PS-48025-005-001
Sales Drawing	SD-48025-009-001
Test Summary	TS-48025-009-001

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION