

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151360703

Status:


Active

Overview:

MicroClasp Wire-to-Board System

Description:

MicroClasp-to-MicroClasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 7 Circuits, White



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	15136
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp-to-MicroClasp
Overmolded	No
Overview	MicroClasp Wire-to-Board System
Product Name	MicroClasp
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191128149440
Physical	
Cable Length	300.00mm
Circuits (Loaded)	7
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	10.494/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.28mm
Wire Size AWG	22
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2012341710-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15136 Series

Mates With

MicroClasp Vertical Header [55932](#)

MicroClasp Right Angle Header [55935](#)