

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151350800

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, Single Row, 50.00mm Length, 8 Circuits, Beige

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Cable Assemblies

Series

15135

Application

Signal, Wire-to-Board

Assembly Configuration

Dual Ended Connectors

Connector to Connector

CLIK-Mate-to-CLIK-Mate

Overmolded

No

Overview

CLIK-Mate Wire-to-Board Connectors

Product Name

CLIK-Mate

Taxonomy

Power and Signal Cable Assembl

Type

Discrete Wire Assembly

UPC

191128160421

Physical

Cable Length

50.00mm

Circuits (Loaded)

8

Color - Resin

Beige

Gender

Male-Male

Lock to Mating Part

Yes

Material - Metal

Copper Alloy

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

PBT

Net Weight

2.595/g

Number of Rows

1

Packaging Type

Bag

Pitch - Mating Interface

1.50mm

Plating min - Mating

0.406µm

Plating min - Termination

0.406µm

Single Ended

No

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.10mm

Wire Size AWG

24

Wire/Cable Type

UL 1061

Electrical

Current - Maximum per Contact

2.0A

Voltage - Maximum

100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

2012341679-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15135 Series

Mates With

Bottom-Entry Receptacle [503395](#) . Right Angle, Through Hole Receptacle [503175](#) . Right Angle, Surface Mount Receptacle [502585](#) . Vertical, Through Hole Receptacle [503159](#) . Vertical, Surface Mount Receptacle [502584](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION