

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349580383

Status:


Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 38 Circuits, Polarization Option A, Black, Tray



Documents:	
3D Model	Application Specification 349590001-AS-CH-000 (PDF)
3D Model (PDF)	Application Specification AS-34959-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-34959-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34958
Application	Automotive, Power, Signal, Wire-to-Board
Comments	30 x 0.50mm blades = 4.0A; 8 x 1.20mm blades = 16.0A
Component Type	PCB Header
Overview	Mini50 Connection Systems
Product Name	Mini50
Taxonomy	PCB Headers and Receptacles
UPC	191128857185
Physical	
Breakaway	No
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	6.372/g
Number of Rows	3
Orientation	Vertical
PC Tail Length	3.07mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34958 Series

Mates With

Mini50 Unsealed Receptacle [349590383](#) , [349590390](#)

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

349590001-AS-CH-000, AS-34959-001-001

PS-34959-001-001

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION