

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2147522042

Status:


Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Gold (Au) Plating, 4 Circuits, Black



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	214752
Application	Power, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Overmolded	No
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	193264585960
Physical	
Cable Length	300.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	15.958/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	18
Wire/Cable Type	Discrete Wire, UL 10002
Electrical	
Current - Maximum per Contact	8.5A
Voltage - Maximum	300V AC/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2147522041-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

214752 Series

Mates With

Micro-Fit 3.0 Receptacle Housing 43645

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION